



The sleeve is used to effectively spread the supported load and enhances lagging facilities and vapour seal.

| I/D Size | Material Size |
|----------|---------------|
| 45 | 100 x 24g |
| 54 | 100 x 24g |
| 60 | 100 x 24g |
| 65 | 100 x 24g |
| 70 | 100 x 24g |
| 76 | 100 x 24g |
| 83 | 100 x 24g |
| 89 | 100 x 24g |
| 95 | 100 x 24g |
| 102 | 100 x 24g |
| 108 | 100 x 24g |
| 114 | 100 x 24g |
| 121 | 100 x 24g |
| 127 | 100 x 24g |
| 133 | 100 x 24g |
| 139 | 100 x 24g |
| 146 | 100 x 24g |
| 152 | 100 x 24g |
| 159 | 100 x 24g |
| 168 | 100 x 24g |
| 173 | 100 x 24g |
| 178 | 100 x 24g |
| 186 | 100 x 24g |
| 193 | 100 x 24g |
| 199 | 100 x 24g |
| 208 | 100 x 24g |
| 219 | 100 x 24g |
| 225 | 100 x 24g |
| 232 | 100 x 24g |
| 244 | 100 x 24g |
| 252 | 100 x 24g |
| 259 | 100 x 24g |
| 268 | 100 x 24g |
| 273 | 100 x 24g |
| 283 | 100 x 24g |
| 290 | 100 x 24g |
| 299 | 100 x 24g |
| 308 | 100 x 24g |
| 316 | 100 x 24g |
| 323 | 100 x 24g |
| 332 | 100 x 24g |
| 344 | 100 x 24g |
| 356 | 100 x 24g |
| 363 | 100 x 24g |
| 373 | 100 x 24g |
| 384 | 100 x 24g |
| 394 | 100 x 24g |
| 406 | 100 x 24g |

| I/D Size | Material Size |
|----------|---------------|
| 76 | 125 x 20g |
| 83 | 125 x 20g |
| 89 | 125 x 20g |
| 95 | 125 x 20g |
| 102 | 125 x 20g |
| 108 | 125 x 20g |
| 114 | 125 x 20g |
| 121 | 125 x 20g |
| 127 | 125 x 20g |
| 133 | 125 x 20g |
| 139 | 125 x 20g |
| 146 | 125 x 20g |
| 152 | 125 x 20g |
| 159 | 125 x 20g |
| 168 | 125 x 20g |
| 173 | 125 x 20g |
| 178 | 125 x 20g |
| 186 | 125 x 20g |
| 193 | 125 x 20g |
| 199 | 125 x 20g |
| 208 | 125 x 20g |
| 219 | 125 x 20g |
| 225 | 125 x 20g |
| 232 | 125 x 20g |
| 244 | 125 x 20g |
| 252 | 125 x 20g |
| 259 | 125 x 20g |
| 268 | 125 x 20g |
| 273 | 125 x 20g |
| 283 | 125 x 20g |
| 290 | 125 x 20g |
| 299 | 125 x 20g |
| 308 | 125 x 20g |
| 316 | 125 x 20g |
| 323 | 125 x 20g |
| 332 | 125 x 20g |
| 344 | 125 x 20g |
| 356 | 125 x 20g |
| 363 | 125 x 20g |
| 373 | 125 x 20g |
| 384 | 125 x 20g |
| 394 | 125 x 20g |
| 406 | 125 x 20g |
| 416 | 125 x 20g |
| 423 | 125 x 20g |
| 433 | 125 x 20g |
| 444 | 125 x 20g |
| 456 | 125 x 20g |

| I/D Size | Material Size |
|----------|---------------|
| 76 | 150 x 20g |
| 83 | 150 x 20g |
| 89 | 150 x 20g |
| 95 | 150 x 20g |
| 102 | 150 x 20g |
| 108 | 150 x 20g |
| 114 | 150 x 20g |
| 121 | 150 x 20g |
| 127 | 150 x 20g |
| 133 | 150 x 20g |
| 139 | 150 x 20g |
| 146 | 150 x 20g |
| 152 | 150 x 20g |
| 159 | 150 x 20g |
| 168 | 150 x 20g |
| 173 | 150 x 20g |
| 178 | 150 x 20g |
| 186 | 150 x 20g |
| 193 | 150 x 20g |
| 199 | 150 x 20g |
| 208 | 150 x 20g |
| 219 | 150 x 20g |
| 225 | 150 x 20g |
| 232 | 150 x 20g |
| 244 | 150 x 20g |
| 252 | 150 x 20g |
| 259 | 150 x 20g |
| 268 | 150 x 20g |
| 273 | 150 x 20g |
| 283 | 150 x 20g |
| 290 | 150 x 20g |
| 299 | 150 x 20g |
| 308 | 150 x 20g |
| 316 | 150 x 20g |
| 323 | 150 x 20g |
| 332 | 150 x 20g |
| 344 | 150 x 20g |
| 356 | 150 x 20g |
| 363 | 150 x 20g |
| 373 | 150 x 20g |
| 384 | 150 x 20g |
| 394 | 150 x 20g |
| 406 | 150 x 20g |
| 416 | 150 x 20g |
| 423 | 150 x 20g |
| 433 | 150 x 20g |
| 444 | 150 x 20g |
| 456 | 150 x 20g |

| I/D Size | Material Size |
|----------|---------------|
| 76 | 200 x 20g |
| 83 | 200 x 20g |
| 89 | 200 x 20g |
| 95 | 200 x 20g |
| 102 | 200 x 20g |
| 108 | 200 x 20g |
| 114 | 200 x 20g |
| 121 | 200 x 20g |
| 127 | 200 x 20g |
| 133 | 200 x 20g |
| 139 | 200 x 20g |
| 146 | 200 x 20g |
| 152 | 200 x 20g |
| 159 | 200 x 20g |
| 168 | 200 x 20g |
| 173 | 200 x 20g |
| 178 | 200 x 20g |
| 186 | 200 x 20g |
| 193 | 200 x 20g |
| 199 | 200 x 20g |
| 208 | 200 x 20g |
| 219 | 200 x 20g |
| 225 | 200 x 20g |
| 232 | 200 x 20g |
| 244 | 200 x 20g |
| 252 | 200 x 20g |
| 259 | 200 x 20g |
| 268 | 200 x 20g |
| 273 | 200 x 20g |
| 283 | 200 x 20g |
| 290 | 200 x 20g |
| 299 | 200 x 20g |
| 308 | 200 x 20g |
| 316 | 200 x 20g |
| 323 | 200 x 20g |
| 332 | 200 x 20g |
| 344 | 200 x 20g |
| 356 | 200 x 20g |
| 363 | 200 x 20g |
| 373 | 200 x 20g |
| 384 | 200 x 20g |
| 394 | 200 x 20g |
| 406 | 200 x 20g |
| 416 | 200 x 20g |
| 423 | 200 x 20g |
| 433 | 200 x 20g |
| 444 | 200 x 20g |
| 456 | 200 x 20g |

Other i/d Sizes and Lengths Available On Request